

# Product Specification PDF

Date	<b>Correct as of 25th Apr 2019</b>
Brand	<b>C.K</b>
Product	<b>T5421</b>
Description	<b>MightyRod PRO Cable Rod Standard Set 10m</b>
Barcode	<b>5013969950649</b>
Commodity code	<b>8205598000</b>
Country of origin	<b>TW</b>



## Features & Benefits

~ Triple bonded steel connectors for extreme torsion and tensile strength □ glued, indented and crimped ~ 10 meters of 100% splinter-proof rods ~ 4 rod flexibilities for overhead, under floor, tight angled and obstructed runs ~ Super tough □MIGHTY-FIX□ zinc plated steel connectors □ tensile strength in excess of 275kg ~ Super flexible, low friction, Spira-FLEX rod for tight angled access points ~ Accessories: flexi lead (mini-flex), ring, hook, gender changer, flat bullet, domed bullet, in-line swivel ~ Total contents: 2 x 1m rods 7 mm Ø / 7 x 1m rods 6 mm Ø / 1 x Rod SpriaFlex 4 mm Ø / 1 x FlexiLead / 1 x Hook / 1 x Flat Bullet / 1 x Domed Bullet / 1 x Ring / 1 x Gender Changer / 1 x In-line Swivel

## Applicable Standards

### Health & Safety

None applicable

### Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	0	20
Width mm	45	45	0	1320
Depth mm	45	45	0	230
Height mm	1300	1300	0	180
Weight	935	935	0	19.6
Packaging Information	Card use	0	0	Case
	Card gms	0	0	900
	Plastic use	0	0	-
	Plastic gms	0	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0