



DCF886D2

18V XR Li-Ion Brushless Impact Driver

Selling Proposition

- Latest generation 18V XR Li-Ion Brushless Impact Driver featuring NEW XR 2.0Ah Li-Ion battery technology
- Brushless motor provides improved runtime and durability
- 2.0Ah XR Li-Ion slide pack batteries with state of charge gauge offers user peace of mind
- 3 LED 'Halo' ring provides maximum illumination of work piece
- 6.35mm 'drop in' keyless hex driver allows for quick, one handed fitment
- Aluminium front housing provides greater heat dispersion increasing motor life

Standard Equipment

- 2 x 2.0Ah XR Li-Ion battery packs with state of charge indicator
- Multi-voltage XR charger
- Belt hook
- Magnetic bit holder
- Heavy duty kitbox

Warranty Specifications

- 3 year limited warranty
- 30 Tage-Geld-zurück-Garantie
- 1 Year Free Service Contract

Specifications

Battery chemistry	XR Li-Ion
Voltage	18 V
Kapazität	2.0 Ah
Max Torque	165 Nm
Abgabeleistung	280 Watt
No Load Speed	0 - 2800 rpm
Impacts per Minute	0 - 3200 ipm
Max. Bolt Diameter	M12