

KERN OBE 124C825

KERN

Our all-round compound microscope as a comprehensive digital solution for schools, training and laboratories



Supported operating systems	Win XP
	Win Vista
	Win 7
	Win 8
	Win 10

Interface	
Interfaces	USB 2.0

Ocular	
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10 x
Ocular visual field	18 mm
Ocular diameter	23,2 mm

Illumination	
Illuminance	Transmitted light
Illumination type incident light	none
Illumination type transmitted light	LED
Illumination intensity transmitted light	3 W
Illumination dimmable	Transmitted light
Filter possible	✓

Focussing	
Field of view [Min]	0,18 mm
Field of view [Max]	4,5 mm
Torque regulation	✓
Fine drive minimum	0,002 mm
Focusing mechanism	coaxial coarse and fine drive

Camera	
Cameratype	USB2 Microscope camera - C-Mount
Camera - Resolution	5,1 MP
Camera - Sensor type	CMOS
Camera - Sensor size	1/2,5"
Camera - Colour depth	Colour
Camera - Framerate	6,8 - 55 fps
Camera- Mounting types	C-mount thread
Camera - Exposure method	Rolling Shutter

Power Supply	
Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter

Category

Brand	Optics
Product category	Microscope
Product group	Digital microscope set
Product family	OBE-S

Construction

Dimension (W×D×H)	360×150×390 mm
Optical system	Finite
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Tube type	Siedentopf
Light distribution	20:80
Contrasting methods	Bright field Darkfield (optional)
Standard objectives	4× 10× 40×
Lens quality	achromatic
Nosepiece screw-in locations	4
Eyepieces fixed	✓
Interpupillary distance [Min]	50 mm
Interpupillary distance [Max]	75 mm
Diopter adjustment	one-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5
Colour temperature	6000 K

Functions

Camera - Applicable software	external (OXM 901, OXM 902)
------------------------------	-----------------------------

KERN OBE 124C825



Our all-round compound microscope as a comprehensive digital solution for schools, training and laboratories

Plug-in power supply / adapter for countries - included with the delivery

EURO

AUS

Plug-in power supply / adapter for countries - optional

UK

US

CH

Input voltage power supply / power [Max]

100 - 240 V

Input voltage device / power [Max]

5 V, 1 A

Environmental conditions

Storage temperature [Min]

-5 °C

Storage temperature [Max]

40 °C

Approval

CE mark



Packing & Shipping

Delivery time

1 d

Dimensions packaging (W×D×H)

560×440×330 mm

Net weight

5,768 kg

Shipping method

Parcel service

Net weight approx.

6 kg

Gross weight approx.

8 kg

Shipping weight

16,3 kg

Pictograms

STANDARD



OPTION

