



AGELED2X5



Features

High specification fully enclosed linear luminaire.

Microprism diffuser for enhanced photometric performance.

Robust steel construction.

Suitable for surface and suspension.

Ideal for most commercial and educational applications.

LED lifespan L70 54,000 hours.


General Information

Lamp Type	LED
Colour / Finish	White
IP Rating	IP20
IK Rating	IK07
Class Protection	1
Internal / External	Internal
Surface / Recessed / Suspended	Surface/Suspended
Warranty (Years)	5
CE Mark	Yes
Length (mm)	1510
Width (mm)	190
Height (mm)	55
Accessories	ASK1

Technical Information

Wattage	54W
Lumens Delivered	5291lm
Lm/W	98lm
CRI	Ra 80
CCT	4000k
Input	230V
Hertz	50/60Hz
Operating Temp	-20°C to 50°C

Datasheet generated from <https://onetimepim.com> last updated Friday, March 26, 2021 11:29:35 AM



Code	A	B	C	FPL
AGELED2X4	1230	190	55	600
AGELED2X5	1510	190	55	880