



JetNet 3710G
Industrial 8 FE + 2 GbE Unmanaged PoE Switch

- 8 10/100 TX plus two 10/100/1000TX uplink ports
- 8 PoE port with 48VDC PWR input
- 802.3af compliant with total power budget 65W
- 2 GbE ports for larger uplink bandwidth
- Support QoS for optimizing video and VoIP stream
- Active port failure alarm
- 25~70°C operating temperature

Facts

General description

Part number	F00N3710000000
Life cycle status	Mature
Warranty	Up to 5 years

Interface

Total ports number	10
10/100TX ports	8
10/100/1000TX ports	2
DI/DO (dry relay)	1 relay DO with 1A/24VDC ability
DC power input	1 x DC 48V
PoE ports	8
Power feeding mode	4578 (B)
PoE mode	IEEE 802.3af
System PoE budget	65W@48V 70°C

Features

Switch type	Unmanaged
-------------	-----------

SW/Protocol

Traffic priority (QoS)	Yes
Event alarm	Port Alarm

Mechanical

Housing/protection (IP)	IP30 Aluminum
Dimension (HxWxD mm)	149 x 66 x 131.2
Mounting	DIN Rail
Operating temperature	-25~70°C

Certification

Regulatory/approval	CE/FCC
RoHS	Yes

People & Technology. Connected.

We are a people company. Our experienced, skilled and passionate people empower you to meet your challenges through best-in-class, user-friendly solutions. We are a technology company. We help you optimize processes through our software, hardware and services, and through our support. Connecting people and technologies gives you the means to accomplish your goals and ambitions, and gain a competitive edge in today's digitalized world.

Visiting address HQ: Stora Varvsgatan 13a

SE - 211 75 Malmö, SWEDEN

[+46 40 35 86 00](tel:+4640358600) (tel:+46 40 35 86 00)

info@beijerelectronics.com (mailto:info@beijerelectronics.com)