

# LED LENSER® Police Tech Focus

The original twist focusing classic from LED Lenser. Simply twist the head to focus the integrated Advanced Focus System optics into a flawless flood beam (near) or intense spot beam (distance). The tactical styling of this torch with its diamond design knurling on the barrel and straighter, more defined head shape results in a large grip area that is welcomed by professionals on the move such as Police and other Emergency Teams as well as professional and amateur handymen alike. Superior materials such as aircraft-grade aluminium housing and gold-plated contacts ensure that this rugged torch won't let anybody down. The Police Tech Focus can deliver a fantastic 115 lumens and on the low beam option, still bright enough for most everyday tasks, will run for around 50 hours off its 3 AAA batteries (supplied).

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the-art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Medium sized classic twist-focus tactical styled torch that is an essential for utility belt or toolbox.
- Energy efficient CREE Power LED Light Chip
- State-of-the-art, reliable German engineering
- Advanced Focus System™ Optics. Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Classic twist focus
- Dynamic Switch™. Single switch light selection -Power, Low Power, Boost
- Robust, yet lightweight aircraft-grade aluminium housing
- User-friendly modular design
- Corrosion resistant gold plated contacts for better conductivity
- Superior rear tail cap switch
- Water and dust resistant. IPX54

## Technical Information

Size: 126 x 32mm Ø

Power: 115 lumens max

Run Time: up to 52 hours

Beam Distance: up to 220m

Weight: 144grams

Supplied with : Wrist-strap, belt/storage pouch and Duracell® batteries (3xAAA)

Code	Colour	Packaging	Barcode
7438	Black	Gift Box	4029113743808
7438TP	Black	Test-It	4029113743753
7438G	Titanium	Gift Box	4029113743846
7438	Blue	Gift Box	4029113743860