



Part Number : [1600740001](#)

Product Description : MX150 Mat-Sealed Female Connector Assembly, Dual Row, 20 Circuits, UL 94V-0, Keying Option A, without Connector Position Assurance, Black

Series Number : 160074

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[1600740001 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[AS-33472-100-001.pdf](#)

[AS-33472-100-CH-001.pdf](#)

[AS-33472-100-FR-001.pdf](#)

[AS-33611-001-001.pdf](#)

[PS-160074-0001-001.pdf](#)

[1600742276-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Dodecamethylcyclohexasiloxane;

	Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	160074
Description	MX150 Mat-Sealed Female Connector Assembly, Dual Row, 20 Circuits, UL 94V-0, Keying Option A, without Connector Position Assurance, Black
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Product Name	MX150
UPC	889056421393

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	20
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	24.000/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarization	A
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Use with Part(s)

Description	Part Number
MX150 Sealed Receptacle Cavity Plug	<u>343454001</u>
MX150 Female Terminals	<u>33001</u>
MX150 Female Terminals	<u>33012</u>