



Combinations for connectors in Gel filled boxes

| Connector | Green | Yellow | Red | Blue | Black | White | Grey | Orange | Purple | Brown | Light Blue | Light Green | Light Yellow | Light Red | Light Blue | Light Green | Light Yellow | Light Red |
|----------------|-------|--------|-----|------|-------|-------|------|--------|--------|-------|------------|-------------|--------------|-----------|------------|-------------|--------------|-----------|
| SC-4 0240-PP10 | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |

SC-4 0240-PP10

E1441297

Splicing Connector, 4-Conductors, 0.2-4.0mm², AWG 28-12, with Lever



Product Properties:

| | |
|---|------------------------|
| Number of clamp positions (device side) | 4 . |
| Type of locking/unlocking | Lever |
| Nominal voltage | 450 V |
| Nominal current | 32 A |
| Suitable for solid conductors | Yes |
| Transparent | Yes |
| Number of clamp positions | 4 . |
| With operation lever | Yes |
| Suitable for solid core | Yes |
| Suitable for flexible core | Yes |
| Suitable for multi-wire core | Yes |
| Strip length | 12 mm |
| Colour | Green |
| Operating temperature | -40-105 °C |
| Connector type | Topplämma, öppningsbar |
| Flammability rating (UL94) | V2 |

Dimensions:

| | |
|---|-----------------------|
| Max. AWG-size | 12 |
| Min. AWG-size | Other |
| Nominal cross section (device side) | 0.2-4 mm ² |
| Nominal cross section (installation side) | 0.2-4 mm ² |

| | |
|--|-----------------------|
| Cable diameter | 1-4 mm |
| Conductor cross section flexible (fine-strand) with cable end sleeve | 0.2-4 mm ² |
| Conductor cross section solid (solid, stranded) | 0.5-4 mm ² |
| Width | 90 mm |
| Height | 11 mm |
| Strip length | 12 mm |
| MOQ | 10 . |
| Unit | pck |
| Nominal cross section | 0.2-4 mm ² |
| Length | 25 mm |
| Nominal voltage | 450 V |

Approvals:

| | |
|----------------------------|-----|
| Approved according to CE | Yes |
| Approved according to TUV | Yes |
| Approved according to UKCA | Ja |

Compliance:

| | |
|-------------------------|------------------------------------|
| Conflict Minerals | N/A, Contains no conflict minerals |
| Iron and Steel Sanction | Contain no Iron or Steel |
| REACH | No SVHC (Latest. 04 Feb 2026) |
| RoHS | RoHS 3 (2015/863) |
| SCIP | Not Applicable |
| US TSCA | No (5 PBT Subs, Feb 2021) |
| ECCN (EU) | No CLASS |

Other information:

| | |
|--------------------|---|
| ETIM-Class | EC000446 - Screwless terminal |
| ETIM-Release | 9.0 |
| Trademark | NEMIQ |
| Product Group | Splicing Connectors - Consumer pack |
| Search Description | SKH2023ERIK1 ENR2023V ANSLUTNINGSKLÄMMA, EFO2025H |
| Alternative SKU | SC-40240-PP10 |
| E-no | E1441297 |

Logistic information:

| | |
|-------------------|--|
| Barcode | 733117641175 |
| Country of origin | CN |
| E-no | E1441297 |
| Item status | Stock item, normally in stock with reservation for in between sales. |
| MOQ | 10 . |
| Stock code | SC-4 0240-PP10 |

Taric code

85369010

Unit

pck

*We reserve the right to make technical changes and disclaim any typographical errors.

Nelco Contact AB - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - order@nelco.se - www.nelco.se