

QUICK CAB PCQ 404017 G



Sample photo

Order symbol: CAB PCQ 404017 G
Product nbr: 8113488
Description: Cabinet, PC
Remarks: Grey cover

EAN: 6418074011183
EI. number:
 Finland: 3421982
 Electric No. Italy: 7681050
 Electric No. Sweden: 2540101

Including: Base with screws for mounting plate/DIN-rail, internal corner plugs, cover with PUR gasket and CS 12137 cover screws.

Dimensions:		Length	Width	Height	Accessories:		
mm:		400	400	170	EKIV 37	DIN-35 Mounting rail	
inch:		15.7	15.7	6.7	FP A 44	Swing-out door/Front plate	
Materials:					MB 12225 AL	Swing door set	
Material:		Polycarbonate		FP 18x2-44	Front plate		
Base colour:		RAL 7035 -light grey		EKI EXT 44	Extension frame		
Cover screws material:		Polyamide		DRF 43/44	DIN rail frame set		
Cover colour:		RAL 7035 -light grey		PAT 12040	Hinge set		
Cover screws colour:		RAL 5023		Rating:			
Gasket material:		Polyurethane		Ingress Protection (EN 60529): IP66/IP67			
Temperatures:					Impact Resistance (EN 62262): IK08		
Temperature °C (short term):		-40 ... 120 °C		Electrical insulation: Totally insulated			
Temperature °C (continuous):		-40 ... 80 °C		Halogen free (DIN/VDE 0472, Part 815): 1			
Temperature °F (short term):		-40 ... 250 °F		UV resistance: UL 508			
Temperature °F (continuous):		-40 ... 175 °F		Flammability Rating: UL 746C 5"			
Accessories:					Glow Wire Test (IEC 695-2-1) °C: 960		
EKIV 44	Mounting plate				NEMA Class: NEMA 1, 4, 4X, 12, 13		
Certificates:					Germanischer Lloyd (GL)		
					SGS Fimko		
					Lloyds Register of Shipping (LR)		
					Gost R		

