



ENGLISH

Datasheet

Precision Brand Steel Feeler Gauge Strips

RS Stock No: 1818121



Specifications:

Precision Brand Feeler Gauge

Material is ground and polished to a precision tolerance

Thicknesses are clearly etched every 6" in decimal and metric

Material: C-1095 Close Grain High

Carbon Spring Steel

Carbon: 0.87-1.10

Phosphorus: 0.036 Max

Silicon: 0.10-0.33

Manganese: 0.27-0.53

Sulphur: 0.050 Max

Temper: Spring

Hardness: 48-62 HRC

Meets Specifications FED-GGG-G-17C For length and thickness only ASTM A-682

Order Code	Manufacturers Code	Thickness	Length	Box Qty
1818121	79-209-603	0.03 x 12.7mm	305mm	5