

## 6 ft SuperSpeed USB 3.0 Cable A to B - M/M

Product ID: USB3SAB6



StarTech.com's 6ft USB 3.0 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.0 standard.

Designed for next-generation SuperSpeed USB device connections, the 6ft USB 3.0 cable offers a throughput of up to 5Gbps when used with a USB 3.0 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 6ft USB 3.0 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 6ft USB 3.0 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

### Certifications, Reports and Compatibility



### Applications

- Superspeed 3.0 data transfer with USB 3.0 compliant devices

### Features

- Cable and Connectors our compliant with USB 3.0 SuperSpeed specifications

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Foil shielded twisted pair
<b>Performance</b>	Type and Rate	USB 3.0 - 5 Gbit/s
<b>Connector(s)</b>	Connector A	1 - USB Type-A (9 pin) USB 3.0 Male
	Connector B	1 - USB Type-B (9 pin) USB 3.0 Male
<b>Physical Characteristics</b>	Cable Length	1.8 m [6 ft]
	Color	Blue
	Product Height	0.000
	Product Length	1.8 m [6 ft]
	Product Width	0.000
	Weight of Product	68 g [2.4 oz]
	Wire Gauge	28 AWG
<b>Packaging Information</b>	Package Height	16 mm [0.6 in]
	Package Length	22 cm [8.7 in]
	Package Width	20 mm [0.8 in]
	Shipping (Package) Weight	77 g [2.7 oz]
<b>What's in the Box</b>	Included in Package	1 - 6 ft SuperSpeed USB 3.0 Cable A to B - M/M

Product appearance and specifications are subject to change without notice.