

## R7S QUARTZ / HALOGEN QUARTZ TUBE



CODE	REF.	V	W	W
<b>► R7S 118 mm</b>				
134161	HR7 2016	240	80	100
134156	HR7 2018	240	120	150
134157	HR7 2020	240	160	200
134158	HR7 2022	240	200	250
134159	HR7 2024	240	230	300
134160	HR7 2026	240	400	500

CODE	REF.	V	W	W
<b>► R7S 78 mm</b>				
134146	HR7 1012	240	48	60
134147	HR7 1016	240	60	75
134148	HR7 1017	240	80	100
134144	HR7 1018	240	120	150
134145	HR7 1020	240	160	200

### Standard

CODE	REF.	V	W	ØxL	
<b>► Grandes longueurs / Long length</b>					
131171	H 624150	24	150	11 x 118	
131179	H 624200	24	200	11 x 118	
131196	H 624300	24	300	11 x 118	
131197	H 624500	24	500	11 x 118	
131998	H 641150	42	150	11 x 118	
131997	H 642200	42	200	11 x 118	
132165	H 641250	42	250	11 x 118	
131992	H 642300	42	300	11 x 118	
130142	H 641400	42	400	11 x 118	
131926	H 641500	42	500	11 x 118	
132000	H 641875	130	75	11 x 118	
131192	H 62103	130	100	11 x 118	
131164	H 61102	130	150	11 x 118	
130157	H 61108	130	200	11 x 118	
131166	H 61124	130	250	11 x 118	
131170	H 61128	130	300	11 x 118	
132019	H 61128 C	130	300	11 x 118	Brilliance®
130163	H 61130	130	500	11 x 118	
130155	H 61130 C	130	500	11 x 118	Brilliance®
130165	H 61134	130	750	11 x 189	
130167	H 61136	130	1000	11 x 189	
130173	H 61142	130	1500	11 x 254	
131977	H 62105	240	100	11 x 118	
<b>130159</b>	<b>H 61106*</b>	<b>240</b>	<b>150</b>	<b>11 x 118</b>	
130544	H 61106 C	240	150	11 x 118	Brilliance®
130161	H 61107	240	200	11 x 118	
131168	H 61126	240	250	11 x 118	
<b>131169</b>	<b>H 61109 R*</b>	<b>240</b>	<b>300</b>	<b>11 x 118</b>	
130160	H 61109	240	300	11 x 118	
131435	H 61109 C	240	300	11 x 118	Brilliance®
131320	H 61109 DEP	240	300	11 x 118	Dépolie/Frosted
<b>131173</b>	<b>H 64702 R*</b>	<b>240</b>	<b>500</b>	<b>11 x 118</b>	
130162	H 164702	240	500	11 x 118	



CODE	REF.	V	W	ØxL	
<b>► Grandes longueurs (suite) / Long length (continued)</b>					
131437	H 64702 C	240	500	11 x 118	Brilliance®
130166	H 61101	240	750	11 x 189	
<b>131927</b>	<b>H 64740 R*</b>	<b>240</b>	<b>1000</b>	<b>11 x 189</b>	
130168	H 64740	240	1000	11 x 189	
130169	H 64740 C	240	1000	11 x 189	Brilliance®
<b>131181</b>	<b>H 64760 R*</b>	<b>240</b>	<b>1000</b>	<b>11 x 254</b>	
130170	H 64760	240	1000	11 x 254	
<b>131199</b>	<b>H 61103 R*</b>	<b>240</b>	<b>1500</b>	<b>11 x 254</b>	
130172	H 61103	240	1500	11 x 254	
<b>132164</b>	<b>H 61104 R*</b>	<b>240</b>	<b>2000</b>	<b>11 x 333</b>	
130174	H 61104	240	2000	11 x 333	
132179	H 6110725	250	200	11 x 118	
132178	H 6110925	250	300	11 x 118	

CODE	REF.	V	W	ØxL	
<b>► Courtes / Short length</b>					
131999	H 648075	130	75	11 x 80	
131975	H 64689	130	100	11 x 80	
131976	H 64694	130	150	11 x 80	
131161	H 61121	130	200	11 x 80	
131191	H 61123	130	250	11 x 80	
131194	H 64599	240	60	11 x 80	
<b>131160</b>	<b>H 164690*</b>	<b>240</b>	<b>100</b>	<b>11 x 80</b>	
130151	H 164690 C	240	100	11 x 80	Brilliance®
<b>131162</b>	<b>H 164695*</b>	<b>240</b>	<b>150</b>	<b>11 x 80</b>	
130143	H 164695 C	240	150	11 x 80	Brilliance®
130548	H 61120 C	240	200	11 x 80	Brilliance®
130158	H 61122	240	250	11 x 80	

\* Filament renforcé / Reinforced filament construction