

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

11-537

Coated with INTERCEPT
TECHNOLOGY[®] and ANSELL GRIP[™]
Technology



Cut



Light Duty

Ultralight cut-resistant industrial safety gloves, offering robust, lasting grip

- **Enhanced grip:** HyFlex[®] 11-537 industrial gloves boast ANSELL GRIP[™] Technology and three-quarter dipped nitrile foam coating, enhancing grip
- **Elevated comfort:** ZONZ[™] Comfort Fit Technology's special blend of yarn and stitches result in a comfortable, ergonomic feel
- **Lightened feel:** These HyFlex[®] gloves' ultralight liner means personal protection with exceptional dexterity
- **Improved durability:** Foam coating, with FORTIX[™] Abrasion Resistance Technology, helps achieve EN and ANSI level 4 abrasion protection
- **Heightened protection:** INTERCEPT[™] Cut Resistance Technology also ensures EN ISO B/ANSI A2 cut protection
- **Reduced surface defect risks:** Silicone-free, the risk of contaminant transfer to metal prior to painting is minimized



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Final assembly
- Handling materials with sharp or rough edges
- Assembly & inspection of components
- Applying finish to materials, products

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-537

Coated with INTERCEPT TECHNOLOGY® and ANSELL GRIP™ Technology

Key Features

- **Three-quarter dipped nitrile coating:** Strong grip, secure handling
- **ZONZ™ Comfort Fit:** Reduced hand fatigue, breathable comfort
- **Ultra-lightweight liner:** Dexterous, maneuverable safety gloves

Technologies



DMF free



Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-537	Finishing: Dipped Coating Material: Foam Nitrile Liner Material: HPPE, Fiber glass, Spandex, Nylon Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	200-270 mm; 8.26-10 inches	Black	• 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

