

| Version Information | |
|-------------------------------------|---|
| Product Name | Microsoft® Arc™ Touch Mouse |
| Product Version | Microsoft Arc Touch Mouse v1.0 |
| Mouse Version | Microsoft Arc Touch Mouse v1.0 |
| Transceiver Version | Microsoft Nano Transceiver v1.0 |
| Product Dimensions | |
| Flat Mouse Length | 5.12 inches (130 millimeters) |
| Flat Mouse Width | 2.32 inches (58.8 millimeters) |
| Flat Mouse Depth/Height | 0.59 inches (15 millimeters) |
| Curved Mouse Length | 4.37 inches (111 millimeters) |
| Curved Mouse Width | 2.32 inches (58.8 millimeters) |
| Curved Mouse Depth/Height | 1.44 inches (36.5 millimeters) |
| Mouse Weight | 3.10 ounces (88 grams) includes 2 AAA alkaline battery; typical battery weight may vary |
| Transceiver Length | 0.72 inches (18.3 millimeters) |
| Transceiver Width | 0.51 inches (13.1 millimeters) |
| Transceiver Depth/Height | 0.17 inches (4.4 millimeters) |
| Transceiver Weight | 0.05 ounces (1.6 grams) |
| Compatibility and Localization | |
| Interface | USB 2.0 Compatible |
| Operating Systems ¹ | <ul style="list-style-type: none"> • Microsoft Windows[®] 8.1, Windows 8, Windows RT 8.1, Windows RT 8, and Windows 7 • Macintosh OS X v10.7-10.9 • Android 3.2 and 4.2 <p>¹Advanced functionality not available with all devices and/or operating systems. See compatibility information at: www.microsoft.com/hardware/compatibility.</p> |
| Top-line System Requirements | <p>Requires a PC that meets the requirements for and has installed one of these operating systems:</p> <ul style="list-style-type: none"> • Windows 8.1, Windows 8, or Windows 7 • 150 MB hard drive space • USB <p>You must accept License Terms for software download. Please download the latest available software version for your OS/Hardware combination. Internet access may be required for certain features. Local and/or long-distance telephone toll charges may apply. Software download required for full functionality of all features.</p> |
| Compatibility Logos | <ul style="list-style-type: none"> • Compatible with Microsoft Windows 8 and Windows RT • Certified USB logo |
| Software Localization | Microsoft Mouse and Keyboard Center software may be installed in Simplified Chinese, Traditional Chinese, English, French, German, Italian, Japanese, Korean, Brazilian Portuguese, Iberian Portuguese, or Spanish. If available, standard setup will install the software in the default OS language. Otherwise, the English language version will be installed. |
| Tracking Technology | |
| Mouse Tracking System | Microsoft-proprietary BlueTrack™ Technology |
| Imaging Rate | Dynamically adaptable to 8000 frames per second |
| X-Y Resolution | 1000 points per inch (39.4 points per millimeter) |
| Tracking Speed | Up to 72 inches (1829 millimeters) per second |
| Wireless Technology | |
| Wireless Frequency | 2.4 GHz frequency range |
| Wireless Range | 15 feet (5 meters) typical. Note: RF range is affected by many factors, such as nearby metallic objects and relative positioning of the mouse and receiver. |
| Product Feature Performance | |
| Mouse Button Features | 2 programmable buttons plus a programmable double-tap region within the scrolling region. |
| Right & Left Button Life | 3,000,000 actuations at no more than 4 actuations per second |
| Mouse Scrolling Features | Standard vertical scrolling |
| Wheel Vertical Scrolling Life | Equivalent to 1,000,000 revolutions |
| Tail Mechanism Life | 40,000 cycles |
| Storage Temperature & Humidity | -40 °F (-40 °C) to 140 °F (60 °C) at < 5% to 65% relative humidity (non-condensing) |
| Operating Temperature & Humidity | 32 °F (0 °C) to 104 °F (40 °C) at <5% to 80% relative humidity (non-condensing) |
| Power Requirements | |
| Battery Type and Quantity | 2 AAA alkaline battery (included) |
| Battery Life | 6 months typical |
| Certification Information | |
| Country of Manufacture | People's Republic of China (PRC) |
| ISO 9001 Qualified Manufacturer | Yes |
| ISO 14001 Qualified Manufacturer | Yes |
| Restriction on Hazardous Substances | This device complies with all applicable worldwide regulations and restrictions including, but not limited to: EU directive 2002/95/EC on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment and EU Registration Evaluation and Authorization of Chemicals (REACH) regulation regarding Substances of Very High Concern. |
| FCC/IC ID | This Class B digital apparatus complies with Part 15 of the U.S. Federal Communications Commission (FCC) rules, Canadian ICES-003, and RSS-210. Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Tested to comply with FCC (U.S. Federal Communications Commission) Standards. For home or office use. The term "IC:" before the certification/registration number only signifies that the Industry Canada technical specifications were met. Model numbers: 1428, Arc Touch Mouse and 1496, Nano Transceiver v1.0; FCC IDs: C3K1428 and C3K1496. IC IDs 3048A-1428 and 3048A-1496. |
| Regulacion para México | La operación de este equipo está sujeta a las siguientes dos condiciones: (1) es posible que este equipo o dispositivo no cause interferencia perjudicial y (2) este equipo o dispositivo debe aceptar cualquier interferencia, incluyendo la que pueda causar su operación no deseada. |
| Agency and Regulatory Marks | <ul style="list-style-type: none"> • CNC Certificate (Argentina) • ACMA Declaration of Conformity (Australia and New Zealand) • TRA Certificate (Bahrain) • ANATEL Certificate (Brazil) • RSS-210 and IC ID, Certificate of Acceptance (Canada) • SUBTEL Certificate (Chile) • CMII Certificate (China) • EIP Pollution Control Mark, EPUP (China) • NTRA Certificate (Egypt) • R&TTE Declaration of Conformity, Safety and EMC (European Union) • WEEE (European Union) • CONATEL Certificate (Honduras) • ETA Certificate (India) • POSTEL Certificate (Indonesia) • MIC Certificate (Israel) • TELEC and VCCI Certificates (Japan) • TRC Certificate (Jordan) • KC Certificate (Kazakhstan) • CCK Certificate (Kenya) • KCC Certificate (Korea) • MPT Certificate (Kuwait) • MOT Certificate (Lebanon) • SIRIM Certificate (Malaysia) • ICTA Certificate (Mauritius) • COFETEL Certificate (Mexico) • ANRT Certificate (Morocco) • NCC Certificate (Nigeria) • TRA Certificate (Oman) • PTA Certificate (Pakistan) • MTC Certificate (Peru) • NTC Certificate (Philippines) • ICT Certificate (Qatar) • GOST and FAC Certificates (Russia) • CITC Letter (Kingdom of Saudi Arabia) • RATEL Certificate (Serbia) • IDA Approval (Singapore) • ICASA Certificate (South Africa) • BSMI and NCC Certificates (Taiwan) • NTC SDoC (Thailand) • CERT Certificate (Tunisia) • UkrSEPRO Certificate (Ukraine) • TRA Certificate (United Arab Emirates) • FCC ID, Grant of Equipment Authorization (USA) • URSEC Certificate (Uruguay) • CONATEL Certificate (Venezuela) • CB Scheme Certificate (International) |
| Windows Certification Kit (WCK) | ID: 1608497 (32-bit) and 1608498 (64-bit) Microsoft Windows 8.1 |

Results stated herein are based on internal Microsoft testing. Individual results and performance may vary. Any device images shown are not actual size. This document is provided for informational purposes only and is subject to change without notice. Microsoft makes no warranty, express or implied, with this document or the information contained herein. Review any public use or publications of any data herein with your local legal counsel.