

FatMax®

FatMax® Tenon Saw - 17-199



- ➔ 11 and 13 teeth per inch for a fine finish
- ➔ Reinforced back for extra rigidity, makes a straighter cut
- ➔ Induction hardened teeth stay sharper twice as long
- ➔ 3 sided precision ground teeth offer razor sharp cutting edges at every stage of the stroke
- ➔ Bi-material handle screwed and ultrasonically welded for comfort and security
- ➔ Handle with marked 45° and 90° angles
- ➔ Finger rest - ergonomic design, useful for extra control when starting a cut

STANLEY	17-199
Length in mm	300
Nr of teeth / inch	11