




Figure similar

transformer SITAS; phases: 1; Pn/Pn(S6)(kVA): 2.5 /13.3; Upri(V): 600-575-550-525-500- 480-460-440-415-400-240-230; Usec(V): 2x115; Isec(A): 10.9-21.8; F(Hz): 50...60; vector group/shielding winding: II0 /0; temperature rise/insulation class: 40 /B; IP00; connection: screw/flat-type connection; mounting: screws; EN 61558-2-1, -2-2, -2-4 >UL/CSA-recognized< >control transformer< >isolation transformer<

General technical data		
product designation		transformer SITAS
product brand name		SIDAC
operating apparent power rated value	VA	2 500
efficiency		0.96
connection method for transformers		II0
certificate of suitability		CE / cRUus
product function		
• temperature monitoring		No
• insulation monitoring		No
• short-circuit and overload proof		No
number of shielding windings		0
short-term vector power	VA	13 300
relative short-circuit voltage	%	1.6
Inputs		
phase number of the inputs		1
input voltage		
• _1 rated value	V	600
• _2 rated value	V	575
• _3 rated value	V	550
• _4 rated value	V	525
• _5 rated value	V	500
• _6 rated value	V	480
• _7 rated value	V	460
• _8 rated value	V	440
• _9 rated value	V	415
• _10 rated value	V	400
• _11 rated value	V	240
• _12 rated value	V	230
electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60
Outputs		
phase number of the outputs		1
output voltage		
• _1 rated value	V	230
• _2 rated value	V	115
electrical output frequency		

- maximum
- minimum

Hz	60
Hz	50

Ambient conditions

thermal class according to IEC 60085		B
ambient temperature rated value	°C	40
protection class IP		IP00

Mechanical data

type of electrical connection		
• at output for main current circuit • at input for main current circuit		screw-type terminals / tab terminals screw-type terminals / tab terminals
fastening method		screws
construction form of the iron core		EI 192/110
width	m	0.194
height	m	0.18
depth	m	0.178

Certificates/ approvals

General Product Approval	other	Environment
--------------------------	-------	-------------



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AM6542-8ED40-0FA0>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM6542-8ED40-0FA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AM6542-8ED40-0FA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM6542-8ED40-0FA0&lang=en

last modified:

4/2/2025