



Datasheet

Stock No: 239-4212

ENGLISH

# RS Pro Insulated Crimp Pin Connector, 26 → 22 AWG, 1.4mm Pin Diameter, Yellow



## Product Details:

### RS Insulated Wire Pin Crimp Terminals

Insulated wire pin crimp terminals made from copper with vinyl insulation (stock number 239-4212 has nylon insulation). Suitable crimp tools for these insulated wire pin crimp connectors are available, see stock numbers 139-704 and 533-279. Stock number 239-4212, the Mini-Yellow wire pin terminal, can only be crimped using crimp tool part number 241-4344.

Mini Yellow 0.2 - 0.5 mm<sup>2</sup>

Red 0.5 - 1.5 mm<sup>2</sup>

Blue 1.5 - 2.5 mm<sup>2</sup>

Yellow 2.5 - 6.5 mm<sup>2</sup>



**ENGLISH**

### RS Pro Range

Conversion table	
M3 / 6 BA	M5/ 2BA
M3.5/ 4BA	M6/ 0BA
M4/ 3BA	

Wire Sizes	
Mini Yellow	0.2 - 0.5 mm <sup>2</sup>
Red	0.5 - 1.5 mm <sup>2</sup>
Blue	1.5 - 2.5 mm <sup>2</sup>
Yellow	2.5 - 6.5 mm <sup>2</sup>

Technical Specification	
Temperature rating	+70°C
Body Material	Copper
Body Plating	Tin

### Note

For a range of general crimp tooling please see 'General Support Tooling' later in this section. For example 157-0875.

### Specifications:

- Wire Size: 26 → 22 AWG
- Colour: Yellow
- Insulation: Insulated
- Pin Diameter: 1.4mm
- Overall Length: 18mm
- Insulation Material: Nylon