

Product Datasheet


ENGLISH


RS Threaded Spacers

Threaded Spacers, also known as Threaded Standoffs are used as a Fastener in a number of industries to create space between two surfaces/objects. Threaded Spacers are used in various electronic applications; a typical application is to space circuit boards for PCB prototyping as well as for use in panel building or to secure cables to external ports and for motherboard mounts. Threaded Spacers are also popular within the automotive industry and are used to connect cylindrical tubes and fuel pipes.

RS offers a range of both Female/Female and Male fully or partially Threaded Spacers available in Brass and Steel.








RS Article	Description	Material	Plating	Н	D	Hole	L	
8066695	Brass Hex Threaded Spacer M4x30mm Female	Brass	Nickel		M4	10	10	30
8066705	Brass Hex Threaded Spacer M4x35mm Female					10	10	35
8066708	Brass Hex Threaded Spacer M4x40mm Female			7		10	10	40
8066702	Brass Hex Threaded Spacer M4x45mm Female					10	10	45
8066711	Brass Hex Threaded Spacer M4x50mm Female					10	10	50
8066601	Threaded spacer, mild steel,M3x5mm,F/F	Steel	Zinc		МЗ	5		5
8066597	Threaded spacer, mild steel,M3x10mm,F/F					10		10
8066584	Threaded spacer, mild steel,M3x15mm,F/F			5		10	10	15
8066581	Threaded spacer, mild steel,M3x20mm,F/F			Э		10	10	20
8066623	Threaded spacer, mild steel,M3x25mm,F/F					10	10	25
8066610	Threaded spacer, mild steel,M3x30mm,F/F					10	10	30
8066566	Threaded spacer, mild steel,M4x10mm,F/F	Steel				10		10
8066550	Threaded spacer, mild steel,M4x15mm,F/F					10	10	15
8066569	Threaded spacer, mild steel,M4x20mm,F/F		Zinc	7	M4	10	10	20
8066594	Threaded spacer, mild steel,M4x25mm,F/F		1			10	10	25
8066626	Threaded spacer, mild steel,M4x30mm,F/F					10	10	30


RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



ENGLISH









RS Article	Description	Material	Plating	Н	D	P1	P2	P3	L
8066714	Brass Hex Threaded Spacer M4x10mm M/F	Brass	Nickel	7			7	8.5	10
8066718	Brass Hex Threaded Spacer M4x12mm M/F						8	10	12
8066727	Brass Hex Threaded Spacer M4x15mm M/F						10	13	15
8066720	Brass Hex Threaded Spacer M4x20mm M/F				M4		10	15	20
8066724	Brass Hex Threaded Spacer M4x25mm M/F					8	10	15	25
8066733	Brass Hex Threaded Spacer M4x30mm M/F					0	10	15	30
8066736	Brass Hex Threaded Spacer M4x35mm M/F						10	15	35
8066730	Brass Hex Threaded Spacer M4x40mm M/F						10	15	40
8066749	Brass Hex Threaded Spacer M4x45mm M/F						10	15	45
8066742	Brass Hex Threaded Spacer M4x50mm M/F						10	15	50
8066632	Brass Hex. Threaded Spacer M5x10mm	Brass	Nickel	8	М5		7	8.5	10
8066635	Brass Hex. Threaded Spacer M5x15mm						10	13	15
8066639	Brass Hex. Threaded Spacer M5x20mm						10	15	20
8066648	Brass Hex. Threaded Spacer M5x25mm						10	15	25
8066641	Brass Hex. Threaded Spacer M5x30mm					8	10	15	30
8066645	Brass Hex. Threaded Spacer M5x35mm					0	10	15	35
8066654	Brass Hex. Threaded Spacer M5x40mm						10	15	40
8066657	Brass Hex. Threaded Spacer M5x45mm						10	15	45
8066651	Brass Hex. Threaded Spacer M5x50mm						10	15	50
8066660	Brass Hex. Threaded Spacer M5x60mm						10	15	60



ENGLISH







RS Article	Description	Material	Plating	н	D	P1	P2	P3	L
8066663	Steel Hex. Threaded Spacer M6x15mm		Nickel				10	12	15
8066667	Steel Hex. Threaded Spacer M6x20mm						10	12	20
8066676	Steel Hex. Threaded Spacer M6x25mm						10	15	25
8066679	Steel Hex. Threaded Spacer M6x30mm					10	10	15	30
8066673	Steel Hex. Threaded Spacer M6x35mm	Steel		10	M6		10	15	35
8066682	Steel Hex. Threaded Spacer M6x40mm						10	15	40
8066685	Steel Hex. Threaded Spacer M6x45mm						10	15	45
8066689	Steel Hex. Threaded Spacer M6x50mm						10	15	50
8066698	Steel Hex. Threaded Spacer M6x55mm						10	15	55
8066691	Steel Hex. Threaded Spacer M6x60mm						10	15	60
8066607	Threaded spacer, mild steel,M3x5mm,M/F		Zinc	5	М3	8	3	4.3	5
8066588	Threaded spacer, mild steel,M3x10mm,M/F	- Steel					6	8.5	10
8066572	Threaded spacer, mild steel,M3x15mm,M/F						8	13	15
8066613	Threaded spacer, mild steel,M3x20mm,M/F						8	15	20
8066629	Threaded spacer, mild steel,M3x25mm,M/F					10	10	15	25
8066617	Threaded spacer, mild steel,M3x30mm,M/F					10	10	15	30
8066578	Threaded spacer, mild steel,M4x10mm,M/F				M4		6	8.5	10
8066562	Threaded spacer, mild steel,M4x15mm,M/F	Steel				8	8	13	15
8066575	Threaded spacer, mild steel,M4x20mm,M/F		Zinc	7			8	15	20
8066604	Threaded spacer, mild steel,M4x25mm,M/F					10	10	15	25
8066590	Threaded spacer, mild steel,M4x30mm,M/F					10	10	15	30

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.