

Portable Band Saw LXT®

DPB184

18V • 51 mm • 0 - 3.2 m/s

Safe, non-sparking metal cutting

A very compact sized band saw weighing only 3.6 kg for metal and, for example, fabric-reinforced hydraulic hoses. Brushless motor and adjustable sawing speed 0-3.2 m / s. Precise sawing thanks to a sturdy torsionally rigid aluminum frame.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Blade Diametre	13 x 0,5 x 730 mm
Blade rapidity	0 - 3,2 m/s
Electronic brake	✓
Max. Cutting Capacity in Steel Pipe	51 x 51 mm
Sound Power Level (L _{WA})	90 dB(A)
Sound Pressure Level (L _{pA})	82 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Cutting metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Cutting metal	1,5 m/s ²
Product Dimensions (L x W x H):	373 x 162 x 223 mm

User benefits

- LED light illuminates the work site
- The rubber coating on the handle ensures a firm working grip
- Cutting metal quickly and without sparks.
- The standard electronics keep the speed constant even under load.
- Variable speed trigger allows operator to adjust speed based on materials or application
- Brushless maintenance-free and long-life motor
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing