

S441 - Classic Rain Trousers

Collection: Classic Rainwear

Range: All Weather Protection

Shell Fabric: 100% Polyester, PVC Coated, 210g

Outer Carton: 24

Product information

Lightweight and easily packable for convenience, these trousers provide comfort and protection in any weather. The fit is roomy for easy layering on top of trousers, with the added benefit of side access pockets. The stud adjustable hem ensures a secure fit around work boots. Unbeatable value for money.

Classic Rainwear

Designed to be worn in foul weather conditions, the Classic rainwear range is not only practical and durable, it offers exceptional value for money. Clever styling and taped seams guarantee maximum comfort and protection.

All Weather Protection

Portwest All Weather Protection is engineered with exceptional fabrics and designs, allowing an easy transition between work and leisure. Tested to withstand the rigours of everyday wear, each garment has been designed and manufactured using the best quality materials and high technology construction techniques to ensure total satisfaction with wear after wear.

Standards

EN 343 Class 3:1 X (WP 5,000mm)



Features

- Extremely water resistant PFAS free Texpel™ Splash Eco fabric finish, water beads away from fabric surface
- Lightweight, waterproof fabric with taped seams prevents water penetration
- Taped seams to provide additional protection
- Fully elasticated waistband for ultimate wearer comfort
- Side access openings
- Stud adjustable hems for a secure fit
- Generous fit for wearer comfort
- REACH compliant PVC coating
- 40+ UPF rated fabric to block 98% of UV rays
- Retail bag which aids presentation for retail sales
- CE certified

S441 - Classic Rain Trousers
Commodity Code: 6210400000

Test House

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
S441YERS	Yellow	56.0	30.0	20.0	0.2800	0.0336	5036108020775	15036108649690
S441YERM	Yellow	56.0	30.0	20.0	0.4610	0.0336	5036108020768	15036108649683
S441YERL	Yellow	56.0	30.0	20.0	0.3260	0.0336	5036108020751	15036108649676
S441YERXL	Yellow	56.0	30.0	20.0	0.3930	0.0336	5036108020782	15036108649706
S441YERXXL	Yellow	56.0	30.0	20.0	0.4000	0.0336	5036108020799	15036108649713
S441YERXXXL	Yellow	56.0	30.0	20.0	0.4140	0.0336	5036108020805	15036108649720
S441YER4XL	Yellow	56.0	30.0	20.0	0.4160	0.0336	5036108057450	15036108649669
S441YER5XL	Yellow	56.0	30.0	20.0	0.4460	0.0336	5036108057467	15036108786050
S441YER6XL	Yellow	56.0	30.0	20.0	0.4630	0.0336	5036108296293	15036108786067