

PREVOS1 SAFETY QUICK COUPLINGS - ISI 06

thread swivel coupler

Profile : ISO 6150B



Part number	Female thread	Min. operating pressure (bar)	Flow rate at 6.00 bar (l/min) ($\Delta P = 0.60$ bar)	ID passage (mm)	Temperature min/max (°C)
ISI 061101SW	G1/4	2.00 / 12.00	833.00	6 mm	-15.00 / 70.00

Part number	Dim. A (mm)	Dim. B (mm)	Dim. C (mm)
ISI 061101SW	172.00	30.00	125.30

