



Product data sheet

Power tools for trade & industry

Optical Level

PRO GOL 26 D



Extremely robust – ideal for outdoor use

The most important data

| | |
|-----------------|------------------|
| Unit of measure | 360 degrees |
| Magnification | 26 x |
| Accuracy | ± 1.6 mm at 30 m |

Part Number 0 601 068 002

Technical data

Technical data

| | |
|----------------------------|------------------|
| Unit of measure | 360 degrees |
| Magnification | 26 x |
| Accuracy | ± 1.6 mm at 30 m |
| Working range | 100 m |
| Dust and splash protection | IP 54 |
| Tripod thread | 5/8" |
| Operating temperature | -10 – 50 °C |
| Storage temperature | -20 – 70 °C |
| Weight, approx. | 1.5 kg |



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Designed for outdoor use due to sturdy metal housing with dust and splash protection (IP54)
- Robust design with built-in target collimator and integrated circular vial
- Compensator lock for safe transport



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

