

Datasheet

## RS Pro Bright Zinc Plated Steel Nylon Insert Locking Nut, M10

RS Stock No: **530-400**



### Product Details

RS Pro nylon insert locking nut made of bright zinc plated steel offers corrosion resistance. This nut is self locking due to glass filled nylon insert and features M10 metric internal threading to couple with threaded rod. The nut is designed to remain secure despite conditions of severe vibration.

### Features and Benefits

- Grade 8 steel, bright zinc plated
- M10 metric threading
- Self-locking due to glass filled nylon insert
- Remain secure despite conditions of severe vibration

**Specifications:**

Finish	Bright Zinc Plated
Material	Steel
Thread Size	M10
Type	Nylon Insert
Grade	8
Specification	DIN 982
Thickness	11.2 to 11.9 mm
Thread Pitch	1.5
Width Across Corners	17.77 mm
Width Across Flats	15.73 to 16 mm
Wrenching Height	6.43 mm

<b>M4 x 10</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9636	<b>M4 x 16</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9642	<b>M4 x 20</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9658	<b>M4 x 30</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9664
<b>M6 x 12</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9759	<b>M6 x 16</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9771	<b>M6 x 20</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9787	<b>M6 x 25</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9793
<b>M8 x 16</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9850	<b>M8 x 20</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9866	<b>M8 x 30</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9872	<b>M8 x 40</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9888
<b>M8 x 40</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  209-9888	<b>M4</b> Nylon insert nuts/Muttern Nyloneinsatz/Tuercas con inserto de nailon/Ecrous à filets rapportés en nylon/Dadi di nylon a intagli  524-304	<b>M6</b> Nylon inserts nuts/Muttern Nyloneinsatz/Tuercas con inserto de nailon/Ecrous à filets rapportés en nylon/Dadi di nylon a intagli  524-326	<b>M8</b> Nylon insert nuts/Muttern Nyloneinsatz/Tuercas con inserto de nailon/Ecrous à filets rapportés en nylon/Dadi di nylon a intagli  530-393
<b>M4</b> Nuts/Muttern/Tuercas/Ecrous/Dadi  525-896 <b>M4</b> Washers/Unterlegscheibe/Arandela/Rondelles/Rondella  525-925	<b>M6</b> Nuts/Muttern/Tuercas/Ecrous/Dadi  525-919	<b>M8</b> Nuts/Muttern/Tuercas/Ecrous/Dadi  527-612	<b>M6</b> Plain washers/Unterlegscheibe/Arandela plana/Rondelles plates/Rondella piana  525-947
<b>M8</b> Plain washers/Unterlegscheibe/Arandela plana/Rondelles plates/Rondella piana  527-634	<b>M10</b> Plain washers/Unterlegscheibe/Arandela plana/Rondelles plates/Rondella piana  527-640	<b>M10 x 20</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  232-8518	<b>M10 x 20</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  232-8518

<b>M10 x 30</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  232-8546	<b>M10</b> Nylon inserts nuts/Muttern Nyloneinsatz/Tuercas con inserto de nailon/Ecrous à filets rapportés en nylon/Dadi di nylon a intagli  530-400	<b>M10</b> Nuts/Muttern/Tuercas/Ecrous/Dadi  527-628
--	---	---

<b>M10 x 50</b> Socket Screw/Buchsenschraube/Tornillo de cabeza hueca/Vis à tête creuse/Brugola  232-8568
--