





ALTW
CONFIDENTIAL
2019-02-22
R&D DEPT.



4Pin Male Connector
Male Pin PCB Layout




Pin Assignments
Front View



Recommended Panel Cut-out

With Liquid Glue






- Note:
- * Important Dimension To Check.
 - * Waterproof Rate: IP67, Unmated
 - * Housing: Thermoplastic, Black
 - * Pin: Copper Alloy, Gold Plated
 - * Nut: Thermoplastic, Black
 - * Gasket: Rubber, Black
 - * Use With Waterproof Cap Or Dust Cap

Panel Thickness Max: 3.0mm

Use Without Waterproof Cap Or Dust Cap

Panel Thickness Max: 4.5mm

- * Gasket and Nut are packed separately in PE bags.



Connector

Nut

Gasket

UNIT: mm	TITLE	Standard	Panel Lock 4Pin M Conn M Pin	SCALE	2:1	SIZE	A4	SHEET	1	OF	1
TOLERANCE											
.X											
.XX											
.XXX											
ANGLES											
REV.											
D											
MC-REV.											
A.3											
QC											
Inspection item											

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	BD-04PMMP-LC700I	DRAWN BY	Ruru	DATE	2019-02-22
DWG NO	BD-04PMMP-LC700I	CHECKED BY	Rita	DATE	2019-02-22
CUSTOMER	ALTW	APPROVED BY	Max	DATE	2019-02-22