

FEATURES

- **Non-Releasable Design:** Provides a secure and permanent fastening solution
- **UV Resistant:** Suitable for outdoor use, maintaining integrity under sunlight exposure
- **High Tensile Strength of 34 kg:** Ensures reliable performance in demanding applications
- **UL 94 V-2 Fire Behaviour:** Meets fire safety standards for added security
- **Wide Maximum Bundle Diameter of 94 mm:** Accommodates larger cable bundles
- **Nylon Material:** Offers flexibility and strength for various applications

RS PRO Nylon Cable Tie, 368 mm Non-Releasable

RS Stock No: 656-054



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO offers a robust nylon cable tie designed for secure and efficient bundling of cables and wires. With a length of 368 mm, this non-releasable cable tie is ideal for applications requiring a strong and permanent fastening solution. Its UV resistance ensures durability in outdoor environments.

General Specifications

Colour	Natural
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	34 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	368 mm
Material	Nylon
Maximum Bundle Diameter	94 mm
Width	4.8 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---