

182.72.104.6672..-BSchrägkugellager

Angular contact ball bearings

7208-B-XL-TVP (Series 72..-B)

main dimensions to DIN 628-1, contact angle $\alpha = 40^\circ$

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	40 mm
D	80 mm
B	18 mm
a	34 mm
D ₁	64,4 mm
d ₁	56,4 mm
D _a max	73 mm
d _a min	47 mm
D _b max	75,8 mm
r ₁ min	0,6 mm
r _{a1} max	0,6 mm
r _a max	1 mm
r _{min}	1,1 mm
α	40 ° Contact angle
m	0,367 kg Mass
C _r	34000 N Basic dynamic load rating, radial
C _{0r}	23500 N Basic static load rating, radial
n _G	10900 1/min Limiting speed
n _B	8600 1/min Reference speed

Cur 1580 N Fatigue limit load, radial

