



Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #640714-1
03P UMNL STR/REL



TE Part #1-179958-4
DYNAMIC D-5200S REC HSG 4P K/X



TE Part #177905-1
POWER DBL LOCK PLUG HSG 12P



TE Part #643030-1
05P UMNL STR/REL



TE Part #3-456403-3
CRIMP,WIRE(062F X 160THK)



TE Part #641776-1
04P UMNL STR/REL



TE Part #177920-1
POWER DBL LOCK PLATE 3.96MM
4POS



TE Part #42660-2
250 FASTON REC 18-14 AWG TPBR
4POS



TE Part #316041-3
DYNAMIC D-5 REC CONT. M L/P



TE Part #1-350779-1
04P UMNL V0 PLUG HSG BROWN

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2350655-5_21.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-2350655-5_21.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2350655-5_21.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets



Instruction Sheet (U.S.)

English