

182.72.104.66NUP2..-EZylinderrollenlager

Cylindrical roller bearings

NUP205-E-XL-TVP2 (Series NUP2..-E)

main dimensions to DIN 5412-1, locating bearing, separable, with cage

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	25 mm
D	52 mm
B	15 mm
B ₃	3 mm
D ₁	43,8 mm
d ₁	34,7 mm
D _a max	46 mm
d _a min	29 mm
d _c min	37 mm
E	46,5 mm
F	31,5 mm
r ₁ min	0,6 mm
r _a max	1 mm
r _{min}	1 mm
m	0,145 kg Mass
C _r	34500 N Basic dynamic load rating, radial
C _{0r}	27500 N Basic static load rating, radial

n_G	17200 1/min	Limiting speed
n_B	11600 1/min	Reference speed
C_{ur}	4400 N	Fatigue limit load, radial



