
Parker Product Datasheet



Quick coupling system with nominal diameter 2.7 for pneumatic, liquids and gas applications up to 35 bar. Available in nickel-plated brass or stainless steel.

PART NUMBER: 20KBKO04MPN
COUPLING HALF: Coupler
CONNECTION TYPE: Tube
FUNCTION: Double Shut-Off
BODY MATERIAL: Brass
CONNECTION SIZE: 3x4 MM

PRODUCT OVERVIEW

Parker’s Series 20 is a mini-industrial coupling with European profile. Coupling system with single-hand operation. High flow rate despite small dimensions.

Markets:
- Industrial
- Life Sciences
- Medical technology
- Chemistry pharmacybr/>- Electronics and energy management
- Transportation
- Machinery construction
- Automotive
- Process

Features/Benefits:

- Mini Industrial coupling
- Single hand operation for easy and fast connection
- European profile is the most representative profile worldwide

TECH SPECIFICATIONS

BRAND	Rectus
APPLICATION	Medical
TECHNOLOGY	Fluid & Gas Handling
VALVE TYPE	Standard Valve
MINIMUM OPERATING TEMPERATURE	-4 °F
MAXIMUM OPERATING PRESSURE	507 psi
APPLICATION	Pharma
REGION OF ORIGIN	Germany
MAXIMUM OPERATING TEMPERATURE	212 °F
LENGTH	34 mm
PRODUCT TYPE	Pneumatic Quick Couplings
QUANTITY PER BOX	10.0
MAXIMUM OPERATING TEMPERATURE	100 °C
MAXIMUM OPERATING PRESSURE	35 bar
CONNECTION TYPE	Tube With hose nut, without spring guard
PRODUCT STYLE	Quick Connect
MINIMUM OPERATING TEMPERATURE	-20 °C
HEX SIZE	9 mm (external)
OPERATION TYPE	Sleeve

DIVISION	Low Pressure Connectors Europe Division
FLOW RATE	1.2 L/min (water)
SEAL MATERIAL	NBR
INDUSTRY	General Industrial
PRODUCT SERIES	Series 20
FOR FLUID TYPE	Water (Industrial, drinking, treated water)
TECHNOLOGY	Pneumatics
WEIGHT	0.011 kg
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
COUPLING HALF	Coupler
DIAMETER	2.7 mm (nominal)
INDUSTRY	Healthcare & Life Sciences
PLATING TYPE	Nickel-Plated
SLEEVE MATERIAL	Brass
APPLICATION	Food & Beverages
INTERCHANGE TYPE	European Profile
BODY MATERIAL	Brass
FUNCTION	Double Shut-Off
COMPATIBLE FITTING	Series 20 Plug
BRAND	Parker
FLOW RATE	130 L/min (air)
DIVISION	Low Pressure Connectors Europe Division
VALVE INCLUDED	Yes
APPLICATION	Industrial Machinery
CONNECTION SIZE	3x4 mm