

CZL120-10RA



CU 90DEGREE LUG 120SQMM M10



General Information

Extended Product Type	CZL120-10RA
Product ID	7TBH007940R0326
EAN	5415022378412
Catalog Description	CU 90DEGREE LUG 120SQMM M10
Long Description	Copper One-Hole Right Angle Metric Lug, Standard Barrel, Cable Size 120mm ² , Stud Size M10, Length 42.7mm, Flat 24.5mm, Hole Spacing 12mm

Ordering

EAN	5415022378412
Minimum Order Quantity	600 piece
Customs Tariff Number	8536904000

Dimensions

Product Net Weight	83.929 g
--------------------	----------

Container Information

Package Level 1 Width	199.898 mm
Package Level 1 Height	102.108 mm
Package Level 1 Depth / Length	72.898 mm
Package Level 2 Units	600 piece
Package Level 2 Width	320.04 mm
Package Level 2 Height	220.98 mm
Package Level 2 Depth / Length	215.9 mm
Package Level 3 Units	600 piece

Additional Information

Brand / Label	Spec-Kon
Insulation Material	None
Material	Copper
Product Main Type	COMPRESSION CONNECTORS
Product Name	COPPER LUG
Product Type	Copper One-Hole 90 Degree Metric Lug

UPC

786210082851

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	CZL120-10RA
Instructions and Manuals	CZL120-10RA

Classifications

ETIM 6	EC001051 - Tube cable lug for copper conductors
UNSPSC	39121405
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

