



New Quick Clamping Shaft Collar

Inch Dimensions

Part Number	Bore (in)	OD (mm)	Width (mm)
QCL-6-A	0.375	38	10
QCL-8-A	0.500	38	10
QCL-10-A	0.625	38	10
QCL-12-A	0.750	50	13
QCL-16-A	1.000	50	13
QCL-18-A	1.125	50	13
QCL-20-A	1.250	75	15
QCL-22-A	1.375	75	15
QCL-24-A	1.500	75	15

Metric Dimensions

Part Number	Bore (mm)	OD (mm)	Width (mm)
MQCL-8-A	8	38	10
MQCL-10-A	10	38	10
MQCL-12-A	12	38	10
MQCL-14-A	14	38	10
MQCL-16-A	16	38	10
MQCL-20-A	20	50	13
MQCL-25-A	25	50	13
MQCL-28-A	28	50	13
MQCL-30-A	30	50	13
MQCL-32-A	32	75	15
MQCL-35-A	35	75	15

- Easily adjustable with integrated lever
- No tools required
- Designed for quick repositioning
- Anodized aluminum resists corrosion

**Black sulfuric anodized
finish to resist corrosion**

MIL-A-8625 Type II, class 2

**Easily hand-operated
CAM action lever**

(Patent-pending design)

Gold anodized to improve visibility

**Single-point faced
precision machining
assures face-to-bore
perpendicularity**

**High strength,
low weight aluminum
body and lever**

**Fine-tuning
adjustment for
shaft size deviation**

18-8 stainless steel
metric hardware

