



Main

Range of product	Thorsman
Product name	Goliath 38
Product or component type	Work lamp
Light source	Compact fluorescent tube 38 W

Complementary

Type of installation	Outdoor Indoor
[Ue] rated operational voltage	230 V
Plug pole configuration	2P
Plug standard	European
Luminous flux	2850 lm
Bulb lifespan	8000 h
Colour rendering index	R _a =82
Colour temperature	3500 K
Illuminance	1 m : 1210 lux 3 m : 134 lux
Cable insulation material	Neoprene
Housing material	PC + rubber
Electrical connection	5 m H07RN-F2x1.0 feed power cord
Electrical insulation class	Class II
Marking	F ENEC 15
Height	280 mm
Width	280 mm
Depth	90 mm
Product weight	2.7 kg

Environment

IP degree of protection	IP54
Quality labels	CE ENEC
Ambient air temperature for operation	-15...50 °C