

Han RJ45 module, for patch cables & RJ-I




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 4623
Specification	Han RJ45 module, for patch cables & RJ-I
HARTING eCatalogue	https://harting.com/09140014623

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® RJ45 module
Size of the module	Single module
Description of the module	Single module

Version

Gender	Male
--------	------

Technical characteristics

Insulation resistance	>10 ¹⁰ Ω
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Material properties

California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	2
Net weight	2 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019447
eCl@ss	27440207 Adapter for industrial connectors (module/contact insert)
ETIM	EC002312
UNSPSC 24.0	39121469