Technical sheet

BUMPIX180

2 m extension kit: 1 × 180° post + 3 barriers + 4 fixings

High-performance polyurethane safety barrier designed to secure traffic areas, protect infrastructure and separate pedestrian and vehicle flows. Highly impact-resistant, it absorbs impacts without breaking and immediately returns to its original shape. This range is systematically supplied with suitable fixings to ensure compliant installation; professional installation is strongly recommended. Impact resistance for forklift trucks: 2 tonnes at 7.5 km/h.







Customs code	39269090
EAN	3321360120458

Color : Yellow

Material : Polyurethane

Specifications :

- High-strength polyurethane.
- Progressive impact absorption.
- Returns to its original shape after impact.
- Rounded snag-resistant design.
- Separation of pedestrian and vehicle flows.
- Modular length.
- Virtually maintenance-free.
- Fixings included.
- Professional installation strongly recommended.
- Impact resistance for a 2-tonne truck at 7.5 km/h.
- Test report available on request.

Length (mm)	Height (mm)	Diameter (mm)	Dimensions plate (mm)	Net weight (kg)
2000	1100	180	2 x 90 x 60	28,20

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com