
## BCC A345-0000-20-000-61X5A5-000

**Order Code: BCC0FK5** 







# CE CALOUS



		ea			

Approval/Conformity CE cURus EAC WEEE

**Electrical connection** Cable diameter D 8...10 mm Connection 7/8"-16 UN-Male, angled, 5-pin Number of connectable contacts 5 System Can be fabricated

#### **Electrical data**

600 VDC / 600 VAC Operating voltage Ub Rated current (40 °C) 12.0 A

#### **Environmental conditions**

Ambient temperature -25...85 °C IP rating IP67

#### Material

Subject to change without notice: PV159432

Material contact carrier PUR, PA/PA Material contacts Brass Material cover nut Die-cast zinc Material grip PBT

#### Mechanical data

0.75...1.5 mm<sup>2</sup> Connection cross-section Type of wire mounting Screw terminals

#### Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

### **Connector Drawings**



PIN 1-5 usable