

# LED Bulkhead Lights

---

## Features

- LED slim bulkhead solution for use in construction and site temporary settings
- 10W, 1200lm, 6000K, IP65, wide voltage 110-240V
- Polycarbonate body with a red diffuser is designed to indicate a hazard or boundary.
- Suitable for wall, ceiling, scaffolding bar or hoarding lighting
- Designed with 6x 20mm conduit knockouts options for rear, top and bottom cable entry.
- Integrated LED Tray
- IP65 rating for total protection against dust and low -pressure jets of water from any direction
- 2-year guarantee

## RS PRO 10W 6000K IP65 SLIM BULKHEADS 110-240V

RS Stock No.: 0556563



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

# LED Bulkhead Lights

---

## Product Description

RS PRO's robust and reliable LED bulkheads provide an ideal lighting solution for construction sites, including areas around scaffolding and other confined spaces. Supplied with a red diffuser, designed to signal hazards, or marked boundaries.

## General Specifications

|                         |                |
|-------------------------|----------------|
| Light Source Luminosity | 1200lm         |
| Efficiency              | 120lm/W        |
| Beam Angle              | 120°           |
| Colour Temperature      | 6000K Daylight |
| Light Source            | Integral LED   |
| Construction            | Polycarbonate  |
| Finish                  | Black/RED      |
| Energy Efficiency       | E              |
| Lifespan                | 50,000 Hours   |
| Warranty                | 2 Years        |

## Electrical Specifications

|                 |          |
|-----------------|----------|
| Wattage         | 10W      |
| Voltage Rating  | 110-240V |
| Running Current | 0.046A   |
| Power Factor    | 0.85     |

## Mechanical Specifications

|        |        |
|--------|--------|
| Length | 230mm  |
| Width  | 110mm  |
| Depth  | 100mm  |
| Weight | 0.25Kg |

# LED Bulkhead Lights

---

## Protection Category

|           |      |
|-----------|------|
| IP Rating | IP65 |
| IK Rating | IK06 |

## Operation Environment Specifications

|                     |                |
|---------------------|----------------|
| Working Temperature | -10oC to +40oC |
|---------------------|----------------|

## Approvals

|                           |                |
|---------------------------|----------------|
| Compliance/Certifications | LVD, EMC, RoHS |
| Standards Met             | BS EN 60598-1  |