

OHY45J6

**ABB contact for United States
of America**

General Information

Extended Product Type:	OHY45J6
Product ID:	1SCA022380R8930
EAN:	6417019124049
Catalog Description:	OHY45J6 HANDLE
Long Description:	IP65, NEMA 1, 3R, 12, padlockable with three padlocks in OFF-position, door interlock in ON- position. Screw fixing from the back side of the handle. No screws on the front ensures double insulation. The type and the ordering numbers are for one piece, red-yellow.



Categories

Products » Low Voltage Products and Systems » Switches » Switch
Disconnectors Accessories

Ordering

EAN:	6417019124049
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389099

Dimensions

Product Net Width:	45 mm
Product Net Height:	66 mm
Product Net Depth:	80 mm
Product Net Weight:	0.1 kg

Container Information

Package Level 1 Units:	100 piece
Package Level 1 Width:	45 mm
Package Level 1 Height:	66 mm
Package Level 1 Length:	80 mm
Package Level 1 Gross Weight:	0.1 kg
Package Level 1 EAN:	6417019124049

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
---------------------	---

Additional Information

IIT Publishing Status:	Level 0 - Information enabled
-------------------------------	-------------------------------

Product Main Type:

OHY45

Product Name:

HANDLE

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:

1SCC390030D0203

Classifications

ETIM 5.0:

EC000229 - Handle for power circuit breaker

Object Classification Code:

N/A