

ENGLISH

**Datasheet** 

RS Pro Cartridge Fuse, F, 8A

RS Stock No: 668-5979



## **Product Details**

RS Pro cartridge fuse is current rated for 8 A. This F-speed, glass bodied fuse is ideal for protection of electrical circuits and consumer appliances.



## **ENGLISH**

## **Specifications:**

Body Material	Glass
Breaking Capacity (at Maximum Voltage Rating)	200 A
Current Rating	8 A
Diameter	5.2 mm
Fuse Speed	F
High Rupture Capacity	No
Includes Indicator	No
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Operating Temperature Range	-55 to +125°C
Overall Dimensions	5.2 x 20 mm
Overall Length	20 mm
Resistance	0.0113 Ω
Size Designation	Miniature
Voltage Rating	250 V ac
Standards Met	CSA Certified, UL Listed, RoHS Compliant, PSE Approved