

SPECIFICATION OF HR-4/3AU

Type: Nickel-Metal Hydride Battery		Size : 4/3A	
Capacity ¹⁾	Typical	4000mAh	
	Minimum	3600mAh	
Nominal Voltage		1.2V	
Charging Current x Time		Fast Charge ²⁾ 3000mA x about 1.5h	
Ambient Temp.	Charge Condition	Fast Charge ²⁾ 0~40°C	
	Discharge Condition		0~50°C
	Storage Condition	~30days	-20~50°C
		30~90days	-20~40°C
90days~1year		-20~30°C	
Internal Impedance ³⁾ (after discharge to E.V.=1.0V)		About 15mOhm (at 1000Hz)	
Weight ⁴⁾		about 55g	
Size ⁴⁾ : (Diameter) x (Height)		17.0 x 67.0 mm	

1)Charge: 0.1C×16h, Discharge: 0.2C(E.V.=1.0V) at 25°C

2)Use recommended charging system.

3)After a few charge and discharge cycles under the above 1) condition.

4)With tube.