






REVISONS		DATE	OWN	APPV
NO.	DESCRIPTION			
B1	ADDED -7	ECR-10-013524	29JUN10	TS KB



- △ MEASURED AT THE SECTION 2mm FROM Z.
- 2. PART NO PLUG HOUSINGS TO BE MATED  
 17P: 353027  
 22P: 353028  
 24P: 353029  
 31P: 353031
- 3. RECOMMENDED SCREW: PAN-HEADED, TYPE 2 TAPPING SCREW OF 3DIA X 6LEN(MAX) (JIS B1115, B1122).
- 4. FASTENING TORQUE FOR SCREW: 0.392N·m MAX.
- △ TINE PLATE COLOR: NATURAL
- △ MARKING FOR DISCERNMENT OF THE CONTACTS FINISH. SEE TABLE
- △ CIRCUIT NUMBER REFERRED TO Fig 1.

- △ Z軸より2mmの位置で測定
- 2. 嵌合相手ハウジング型番  
 17P: 353027  
 22P: 353028  
 24P: 353029  
 31P: 353031
- 3. 推奨締め付け: JIS B1115, B1122タップシボのみ。おおよそ  
 締め付け3. 長さ6以下  
 ねじ締め付けトルク: 0.392N·m MAX.
- △ タイン・プレートの色は、自然色
- △ コンタクト仕上識別用マーク: 表参照
- △ 回路番号はFig 1参照のこと



△ Fig 1 CIRCUIT NUMBER

PACKING STYLE	PACKING STYLE	MARKING	CONTACT FINISH	CONTACT FINISH	GOLD PLATED CIRCUIT NO	COLOR	PART NUMBER
梱包仕様	梱包仕様	△ 6	コンタクト仕上	接触状態	金めっき回路番号	色	製品番号
PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	2 <sub>1</sub>	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 16 SELECTIVE-TIN × 78 (BRIGHT)	12, 13, 19, 54, 55 61-63, 77, 80-83, 91-93	NATURAL	2-6123794-1
PAPER BOX ダンボール箱	PLASTIC TUBE プラスチックチューブ	2 <sub>1</sub>	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 16 SELECTIVE-TIN × 78 (BRIGHT)	12, 13, 19, 54, 55 61-63, 77, 80-83, 91-93	NATURAL	1123794-7
PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	0 <sub>1</sub>	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN × 94 (BRIGHT)	— / —	NATURAL	1123794-6
PAPER BOX ダンボール箱	PLASTIC TUBE プラスチックチューブ	3	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN × 94 (BRIGHT)	— / —	NATURAL	1123794-4
PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	2	TIN-LEAD SELECTIVE-TIN	SELECTIVE GOLD × 16 PRE-TIN × 78	12, 13, 19, 54, 55 61-63, 77, 80-83, 91-93	NATURAL	2-1123794-1
PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	1	PRE-TIN × 94	PRE-TIN × 94	— / —	NATURAL	1123794-2
PLASTIC BOX 通い箱	PLASTIC TUBE プラスチックチューブ	0	SELECTIVE-TIN	PRE-TIN × 94	— / —	NATURAL	1123794-1
OUTER 外装	INNER 内装		SOLDERING SIDE 半田付付部	CONTACT SIDE 接触部側			

TOLERANCE UNLESS OTHERWISE SPECIFIED:	
一般公差	
10±	±0.2
30± >10	±0.25
100± >30	±0.3
ANGLE	±3°

DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.01 4 PLC ±0.001 UNLESS OTHERWISE SPECIFIED	DIMENSIONS: mm 0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.01 4 PLC ±0.001 UNLESS OTHERWISE SPECIFIED	TOLERANCES UNLESS OTHERWISE SPECIFIED: 10± ±0.2 30± >10 ±0.25 100± >30 ±0.3 ANGLE ±3°	MATERIAL PBT, BRASS	FINISH SEE TABLE	WEIGHT 35.0g	CUSTOMER DRAWING	TYPYCO ELECTRONICS CORPORATION KAWASAKI, JAPAN	Tyco Electronics Corporation Kawasaki, Japan	NAME 040111 HIGH DENSITY CONNECTOR 94P CAP HOUSING ASSY	PRODUCT SPEC 108-5529	APPLICATION SPEC	SIZE A1	CASE CODE 00779	DRAWING NO 1123794	RESTRICTED TO
-----------------------	------------------------------------------------------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------	------------------------	---------------------	-----------------	------------------	---------------------------------------------------	-------------------------------------------------	---------------------------------------------------------------	--------------------------	------------------	------------	--------------------	-----------------------	---------------