

Housing - HC-D 7-TFL-48/M1PG11S - 1773271

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve housing, for single locking latch, height 48 mm, with screw connection, 1 x Pg11, lateral cable outlet, zinc die-cast



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 122270
Weight per Piece (excluding packing)	73.4 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	48 mm
Width	28 mm
Length	26.5 mm
Wrench size, union nut	18 mm
External cable diameter	7.5 mm ... 12.5 mm

Ambient conditions

Degree of protection of housing (IP)	IP54
	IP65 (with sealing screw)
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-D7, D8, A3, A4, B5, HS2-D7
Type	D7
Housing type	Sleeve housing
Locking type	for single locking latch
No. of cable outlets	1

Housing - HC-D 7-TFL-48/M1PG11S - 1773271

Technical data

General

Cable exit	Lateral
Screw connection	with
Type of the screw connection	1x Pg11
Housing material	Zinc die-cast
Housing surface material	Powder-coated, gray
Cable gland material	Nickel-plated brass
Cable seal material	NBR

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC / GL

Ex Approvals

Housing - HC-D 7-TFL-48/M1PG11S - 1773271

Approvals

Approvals submitted

Approval details

EAC

GL

Accessories

Accessories

Mounting material

Sealing screw - HC-D 7-DS-IP65 - 1686229



Sealing screw, for IP65 protection

Drawings

Dimensioned drawing

