

PRODUCT-DETAILS

GRNY-250-0-C

GROMMETING EXTD .25IN BLK NYL 100FT



General Information

Extended Product Type	GRNY-250-0-C
Product ID	7TAG009750R0034
EAN	5414363023685
Catalog Description	GROMMETING EXTD .25IN BLK NYL 100FT
Long Description	Extruded Grommeting, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Height of 7.11mm (0.28 Inches), Width of 9.40mm (0.37 Inches), Thickness 1.27mm (0.05 Inches), Width Maximum Panel Thickness of 6.35mm (0.25 Inches)

Ordering

EAN	5414363023685
UPC	728494116709

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	15 in 381 mm
Package Level 1 Height	2.25 in 57 mm
Package Level 1 Depth / Length	21 in 533 mm
Package Level 2 Units	5 piece
Package Level 2 Width	12.5 in 318 mm

Package Level 2 Height	12 in 305 mm
Package Level 2 Depth / Length	18 in 457 mm

Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	19960215
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Panel Thickness	0.25 in 6.35 mm
Product Name	NYLON GROMMETING
Product Type	Grommeting
Special Functions	Used to line panel edges and knockouts where the chafing of wires is a concern.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	GRNY-250-0-C
Instructions and Manuals	GRNY-250-0-C

Classifications

ETIM 6	EC002604 - Cable bundle hose
ETIM 7	EC002604 - Cable bundle hose
UNSPSC	39131603
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5393 >> Grommet edging

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

