



Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 2-2324582-0

HSG,REC,FREE-HANGING,DUALROW,EP2.5



TE Part # 1969592-8

HSG,REC,FREE-HANGING,DUALROW,EP2.5



TE Part # 2-1969540-0


HOUSING, PLUG, 20P,DUAL ROW,EP2.5

Customers Also Bought



TE Part #2178474-2

3POS UMNL CAP HSG V0 GW



TE Part #2404460-3

3P RAST 2.5 STD TIMER (5mm pitch)



TE Part #1827395-2

GIC 3.3 REC CONTACT TIN PLATE



TE Part #1747995-1

GHC EYELET 6.2 3POS PLUG HOUSING NATURAL



TE Part #1827385-1

GIC 3.3 PLUG HOUSING 4P



TE Part #2297440-3

MMF,FREE HANGING,PLUG HOUSING




TE Part #5-1241965-4

STD TIMER PLUG HSG 4P W/EXT. LOCKING



TE Part #2297438-3

MMF,FREE HANGING,CAP HOUSING



TE Part #2-2232701-1

NEW GI CONN2.5 PLUG HSG 2P NC



TE Part #1376348-1

5MM POWER KEY CONN REC CONT M

Documents

Product Drawings

HSG,REC,FREE-HANGING,DUALROW,EP2.5

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1969592-0_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2-1969592-0_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1969592-0_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[7-1773461-6_EP2.5_Connector_Series](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[VDE Certificate](#)

English