

230.1604

PLUG
16A 3P 20-25V 60Hz 50Hz Screw
terminals



* Product image may be indicative



EN IEC 60309-1 (2022)
EN IEC 60309-2 (2022)

GENERAL CHARACTERISTICS

Commercial Series	IEC309 Series
Synthetical description	PLUG
Description	
The plug from the IEC309 Series is designed for a rated voltage of 20-25V and a current of 16A. Featuring 3P poles, it operates efficiently at both 50Hz and 60Hz frequencies. With a protection degree of IP44/IP54, it offers reliable performance in moderately demanding environments. The plug is equipped with screw terminals and is compatible with straight type outlets.	
Mounting version	PORTABLE

TECHNICAL CHARACTERISTICS

Rated current	16A
Poles	3P
Rated voltage	20-25V
Working frequency	60Hz
	50Hz
Terminals	Screw terminals

PHYSICAL CHARACTERISTICS

Mounting version	PORTABLE
Colour	VIOLET
Material	THERMOPLASTIC
Protection degree	Splash proof
Protection degree IP	IP44/IP54
Types of available outlets	STRAIGHT
Contact material	CuZn (brass)
Surface treatment contacts	Nickel-plated

DOWNLOAD

Technical drawing [PDF]
Technical drawing [STP]
Technical drawing [DWG]