



Main

Range	Actassi
Product	19" patchcord brush panel
Colour	Light grey (RAL 7035) Dark grey (RAL 7016)
Provided equipment	2 quick fix 19" mountings 1 brush for patch cords

Complementary

Rack unit	1U
Material	Metal sheet: DC01 Plastic part: PA66 GF20 Plastic part: PC Brush peels: PA (polyamide)
Width	0.48 M 484 mm
Height	0.044 M 44 mm
Depth	0.040 M 40 mm
Net weight	0.3 Kg 0.3000 kg

Environment

Ambient air temperature for operation	-10...55 °C 14...131 °F
Standards	IEC 60297 NF C 20-150

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations