

58BA-AS
sparkproof double open end slogging wrenches


		art.	 mm	L mm	A mm	S mm	 g
★	000580904	58BA-AS 11/16	11/16	125	40,5	11,0	150
★	000580905	58BA-AS 3/4	3/4	125	40,5	11,0	150
★	000580906	58BA-AS 7/8	7/8	135	46,2	12,0	195
★	000580907	58BA-AS 15/16	15/16	150	50,3	12,0	245
★	000580954	58BA-AS 31/32	31/32	150	50,3	12,0	245
★	000580908	58BA-AS 1"	1	175	56,9	15,0	335
★	000580909	58BA-AS 1.1/8	1.1/8	190	64,0	15,5	435
★	000580910	58BA-AS 1.1/4	1.1/4	190	64,0	15,5	515
★	000580912	58BA-AS 1.7/16	1.7/16	210	75,0	18,5	800
★	000580913	58BA-AS 1.1/2	1.1/2	220	82,0	18,5	860
★	000580914	58BA-AS 1.5/8	1.5/8	230	86,8	18,5	955
★	000580970	58BA-AS 1.3/4	1.3/4	250	98,0	20,	1225