

FEATURES

- Plan Shank
- Various lengths
- HSS for performance and safety
- Perfect for general workshop and maintenance use

RS PRO HSS Twist Drill Bit, 6.5mm x 101mm

RS Stock No.: 213-168



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Brought to you by RS PRO, a range of jobber drill bits suitable for high-speed metal, wood and plastic drilling. Designed as a twisted drill bit, these attachments guarantee excellent performance and will be an asset to your application. All models are highly reliable and excellent quality.

General Specifications

Drill Bit Type	Twist Drill Bit
Type	Twist
Material	HSS M2
Drilling Application	Construction, electrical or masonry applications

Mechanical Specifications

Overall Length	101mm
Point Angle	118°
Diameter	6.5mm
Flute Length	63mm

Approvals

Compliance/Certifications	DIN 338
---------------------------	---------



RS Stock No.	Diameter(mm)	Overall Length (mm)	Flute Length (mm)
212-991	1.0	34	12
212-985	1.5	40	18
212-979	2.0	49	24
213-089	2.5	57	30
212-963	3.0	61	33
212-957	3.3	65	36
213-073	3.5	70	39
213-067	4.0	75	43
213-051	4.2	75	43
213-023	4.5	80	47
213-045	5.0	86	52
213-039	5.5	93	57
213-095	6.0	93	57
213-168	6.5	101	63
213-146	7.0	109	69
213-130	7.5	109	69
213-124	8.0	117	75
213-118	8.5	117	75
213-102	9.0	125	81
212-929	10.0	133	87
212-913	10.2	133	87
212-907	10.5	133	87
212-884	11.0	142	94
212-878	12.0	151	101
212-935	13.0	151	101