

## 1 B 75

Combination spanner with same size each end

metric

Code	ETIM
6004820	EC002176
EAN	UNSPSC
4010886600481	27-11-17-13
Country of origin	eCl@ss
Germany	21-04-01-05
Customs tariff number	
	82041100



## Article description

- Acc. to DIN 3113, Form A, ISO 3318, ISO 7738
- Sizes 5 and 5.5 mm with hexagon ring, up from size 6 mm with UD profile
- Chrome-vanadium steel 31CrV3, chrome-plated
- Carefully forged and professionally machined
- Ring: 10° offset from shaft, with UD profile for gentle transmission of force
- Overloading indicated by deformation
- The offset ring ensures a better grip on deep-seated or inset nuts or bolts
- Top-grade industrial quality for the hardest of continuous use
- \* not standardised

## Article information

Contents [Qty of pieces]	1	Head height 2 [mm]	26 mm
Net weight [kg]	6,545 kg	Head height 1 [mm]	38 mm
Total length [mm]	810 mm	Width of head 1 [mm]	110,0 mm
Surface	chrome-plated	Mouth position 1	15°
Material	Vanadium steel 31CrV3	Height of offset 1	57,5 mm
Standard	not standardised	Ring profile	bi-hex
Width across flats 1 [mm]	75	Ring offset	10°
Width of head 2 [mm]	153 mm	Weight	14,430 lbs