

TSI Code: 397089051

Price\*: 83.00 GBP



### Main

Range	Spacial
Product name	Spacial SBM
Device application	Multi-purpose
Product or component type	Industrial box
Device short name	SBM
Enclosure type	Flat face box
Enclosure nominal height	300 Mm
Enclosure nominal width	600 Mm
Enclosure nominal depth	120 Mm
Enclosure mounting	Wall mounted
Device composition	1 cover 1 body 6 cover screw
Body type	Single piece body folded and welded
Type of front cover	Plain door
Cover fixing	Half turn metal screw
Lock type	Captive screw PZ2 outside sealed area
Removable parts	Cover by captive screws

### Complementary

Material	Sheet steel
Surface finish	Polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	LR DNV-GL UL BV
IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for storage	-35...60 °C
Ambient air temperature for operation	-35...80 °C
Net weight	6.724 Kg

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	6.724 Kg
Package 1 Height	62.5 Cm
Package 1 width	31.5 Cm
Package 1 Length	15 Cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**