


AxiMax 400 Comm X7R, Ceramic, 0.056 uF, 10%, 100 VDC, X7R, AxiMax, Commercial Standard



Dimensions

D	2.54mm MAX
L	5.08mm MAX
LL	25.4mm MIN
F	0.51mm +0.025/-0.076mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	300

General Information

Supplier:	KEMET
Series:	AxiMax 400 Comm X7R
Description:	AxiMax, Commercial Standard
RoHS:	Yes
Termination:	Tin
Failure Rate:	N/A
Halogen Free:	Yes

Specifications

Capacitance:	0.056 uF
Capacitance Tolerance:	10%
Voltage DC:	100 VDC
Dielectric Withstanding Voltage:	250 VDC
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5% 25C
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	17.86 GOhms